



ENGLISH

Datasheet

PLL Low Bay Light Fitting, 55 W

RS Stock 570-394



Specification:

- High quality luminaire utilising energy saving compact fluorescent lamps.
- Supplied as standard with a choice of 4 x 55w TC-L or 4 x 80w TC-L compact fluorescent lamps, instant high-efficiency lighting with high-output integral 3 hour emergency lighting using 1 lamp enables the product to be specified for applications which traditional high pressure discharge lobays do not have a solution.
- Suitable for surface mounting or suspension and is supplied with 4 fixing points and 3 BESA box entries as standard.
- High quality and intelligently designed reflector system provides precise and controlled optical performance resulting in impressive and superior spacing data (see photometric data), ideal for high mounting applications such as sports halls, warehouses, factories.
- Independent switching circuits enable the product the option of switching off 2 lamps when in mains operation enabling potential power savings