



DEWALT 54V XR FLEXVOLT M-Class Dust Extractor

DCV586MT2



- M-Class Compliant, < 0.1% dust escape through filter, suitable for use on construction sites
- Wireless vac activation by a remote key fob so there is no need to switch on at source for ease of use and saves time
- 2000W Brushless Motor provides powerful and market leading overload protection for increased performance
- Innovative dual filter cleaning system maintains performance during tough construction applications
- Constant suction power even with the finest concrete and wood dust
- A filter is automatically cleaned every 30 seconds reducing filter clogging and delivering constant air flow
- TSTAK® Compatible provides ease of use, enhanced mobility and saves time
- Wet and dry for maximum clean up flexibility
- Audible alarm alerts user if a drop in performance occurs

Description:

The DEWALT 54V XR FLEXVOLT M-Class Dust Extractor is powered by 54V XR FLEXVOLT technology making it the ultimate dust extraction solution for a new generation of cordless tools and the key to unlocking the cordless jobsite. The 2000W brushless motor and high capacity XR FLEXVOLT battery coupled with dual M-Class certified filters with automatic cleaning delivers powerful, constant performance and runtime for the most demanding applications. The extractor features a key fob remote which enables wireless activation of the unit away from the switch for ease of use, saving time and effort. The TSTAK® compatibility enables ease of use, enhanced mobility and flexible storage.

Supplied With:

- 2 x 54V XR FLEXVOLT 6Ah/2Ah batteries
- 1 x 2.4m x 32m Extraction hose
- 1 x 3mm Air Lock adapter
- 1 x Air Lock adapter
- 1 x Fleece dust bag
- 1 x Key fob and strap
- 1 x Fast battery charger

Specifications	
Battery	XR FLEXVOLT Lithium-Ion
Voltage	54 V
Extraction Classification	M Class
Max Airflow	24.7 l/sec
Tank Capacity	11L
Wet/Dry Capacity	7.5L
Hose Length	2.5M
Hose Connection	Air Lock
Hose Diameter	32MM
Weight	7.5KG