

Manifold sub-base VABV-S2-2S-N12-T2

Part number: 560843

FESTO



Data sheet

Feature	Value
Grid dimension	59 mm
Terminal type	44
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
CE mark (see declaration of conformity)	To EU Low Voltage Directive
CE marking (see declaration of conformity)	To UK regulations for electrical equipment
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	610 g
Pneumatic connection, port 2	1/2 NPT
Pneumatic connection, port 4	1/2 NPT
Note on materials	RoHS-compliant
Material plate	Die-cast aluminium