



verso kitted cupboard. Featuring a robust, fully welded steel housing with double, reinforced doors with 2 adjustable height, galvanised steel shelves (75kg U.D.L.), 1x 125mm drawer with 100% extension slides (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1300x550x1000mm.

Breite [mm]: 1300
Tiefe [mm]: 550
Höhe [mm]: 1000
Bruttogewicht [kg]: 83.35
EAN-Code: 5039350124468
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	1
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Shelf load capacity [kg]	75
Door type	Plain
Door height 1 [mm]	925