

KEMET Part Number: 200MS26ACMK1STD
(A902GP200K260A)

MS/A902, Aluminum Electrolytic, 200 uF, 10%, 260 VAC, -20/+60°C



| General Information | |
|---------------------|-----------------------------------|
| Supplier: | KEMET |
| Series: | MS/A902 |
| Dielectric: | Aluminum Electrolytic |
| Description: | Motor Start Aluminum Electrolytic |
| RoHS: | Yes |
| Lead: | Quick Connect |
| AEC-Q200: | No |
| Shelf Life: | 156 Weeks |

| Dimensions | |
|------------|---------------|
| D | 38mm +/-0.5mm |
| L | 116mm MAX |

| Specifications | |
|------------------------|-----------|
| Capacitance: | 200 uF |
| Capacitance Tolerance: | 10% |
| Voltage AC: | 260 VAC |
| Temperature Range: | -20/+60°C |
| Rated Temperature: | 60°C |
| Life: | 500 Hrs |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |