

## M23 cover-s met. for HBM,chain 100mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 9102
Specification	M23 cover-s met. for HBM,chain 100mm
HARTING eCatalogue	<a href="https://harting.com/09156009102">https://harting.com/09156009102</a>

### Identification

Category	Accessories
Series	Circular connectors M23
Identification	Power
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for cable to cable housing With chain (100 mm)

### Technical characteristics

Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
--	--

### Material properties

Material (accessories)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



**Pushing Performance**  
Since 1945

## Material properties

Fire protection on railway vehicles EN 45545-2 (2020-08) + A1 (2023-10)

Requirement set with Hazard Levels R26

## Specifications and approvals

UL / CSA UL 1977 ECBT2.E235076

## Commercial data

Packaging size 5

Net weight 16.59 g

Country of origin Germany

European customs tariff number 74199990

GTIN 5713140184442

eCl@ss 27440208 Cap for industrial connectors

ETIM EC002314

UNSPSC 24.0 39121467