

CONTACTUM



DDS14188MS-P01



14 Way Pop H/Int 100A Sw+2x80A RCD CU + 10 MCB's + 1 RCBO

General	Technical
<p>Box quantity: 1</p> <p>ABC indicator: B</p> <p>Colour: White</p> <p>Fault current protection (RCD): Yes</p>	<p>Associated standards: BS EN 61439-3</p> <p>Rated voltage: 220-250V</p> <p>Rated current: 100A main incomer 80A RCD</p> <p>Frequency: 50-60Hz</p> <p>Wiring system: 2 pole</p> <p>Ambient operating temperature: -5 to 40°C (24hour average not exceeding 25°C)</p> <p>Width in number of modular spacings: 20</p> <p>Nature of supply: AC</p> <p>Rated fault current: 30</p> <p>DIN-rail: Yes</p> <p>Extension possible: Yes</p> <p>With lock: Optional</p> <p>Type of cover: Hinged</p> <p>Material housing: steel</p> <p>Plate thickness cabinet: 1.2mm</p> <p>Plate thickness door/cover: 1.2mm</p> <p>Mounting method: Surface</p> <p>Number of outgoing ways: 14</p>

Source URL: <https://www.contactum.co.uk/content/dds14188ms-p01>