

## FEATURES

- Trace Heating Tape Constant Wattage, Parallel Circuit
- May be looped around an enclosure, avoids localised hot spots
- Available in 3m or 6m cable reels
- Easy to install  
Very flexible

## RS PRO 10W/m Trace Heating Tape Constant Wattage, Parallel Circuit, 240 V, 3m

RS Stock No.:379-722



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

RS PRO range of anti-condensation heating tapes are intended for use to prevent condensation inside electrical and similar cabinets. The tape should not be subjected to temperatures above 200°C and a thermostat may be used to control the tape. Parallel circuit, constant 10W output per metre heating tapes terminated in 1.3m of 2-core mains cable.

Constant wattage heating cables options:

[379-722](#) - 3m cable

[379-738](#) - 6m cable

## General Specifications

<b>Cable Type</b>	Constant Wattage, Parallel Circuit
<b>Self-Regulating</b>	No
<b>Sheath Material</b>	Silicone Rubber
<b>Standard Met</b>	RoHS Compliant
<b>Applications</b>	Frost protection; Water, oil and chemical lines; Sprinkler system mains; Supply piping; Not for use in hazardous areas

## Electrical Specifications

<b>Output Per Metre</b>	10W
<b>Voltage Rating</b>	240Vac

## Mechanical Specifications

<b>Length</b>	3m
---------------	----

## Operation Environment Specifications

<b>Operating Temperature Rating</b>	-70°C to 200°C
-------------------------------------	----------------

## Approvals

### Compliance/Certifications

RoHS Compliance



