

1993 GU-3

Swivel head reversible ratchet 1/2"

Code	ETIM
6144320	EC002218
EAN	UNSPSC
4010886614433	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



1/2" 12,5

Article description

- Especially suitable for use in the automotive sector
- 180° swivelling, with joint lock
- With non-slip metal disc change, fine-toothed (72 teeth) and robust
- Return angle 5°
- Non-slip 2-component handle with suspension hole
- Max. torque 300 Nm
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Drive connector square (male)	12,5 mm
Net weight [kg]	0,535 kg	Return angle	5°
Total length [mm]	287 mm	Number of teeth	72
Total width [mm]	38 mm	Torque (max.) [N·m]	300 Nm
Total height [mm]	38 mm	Handle material	2-components
Surface	chrome-plated	Ratchet head height	40,5 mm
Material	Vanadium steel 31CrV3	Locking type	Ball locking device
Drive connector square (male)	1/2"	Push button release	no