



## Main

Range	OptiLine
Product name	OptiLine 45
Cabling installation system	Pole
Product type	Pole
Type of pole	One-sided
Pole/post surface finish	Powder coated
Pole fixing mode	Free-standing

## Complementary

Colour	Polar white (RAL 9003)
Front opening size	45 mm
Material	Aluminium powder coated
Quantity package 1 / unit	Set of 1
Height	2450 mm
Depth	89 mm
Width	68 mm

## Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
IP degree of protection	IP40

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations