

har-SAB M12/8/5p PAC 5m PVC w/o LED



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 001 2225 100
Specification	har-SAB M12/8/5p PAC 5m PVC w/o LED
HARTING eCatalogue	https://harting.com/09070012225100

Identification

Series	Circular connectors M12
Element	Distribution boxes
Specification	Pre-assembled master cable

Version

Cable length	5 m
Core structure	3x AWG 18 + 16x AWG 22
Total number of ports	8
Number of contacts	5

Technical characteristics

Rated current	9 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

Material properties

Material (cable)	PVC
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 2238 CYJV.E500416 CSA-C22.2 CYJV7.E500416
----------	---

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140277359
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501