

CRGCQ2512J150R

✓ ACTIVE

Neohm | Neohm CRGCQ

TE Internal #: 1-2176350-4

150 ohm, Surface Mount General Purpose Resistor, Thick Film, 2512, 1 W, 5 %, ±100 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Neohm CRGCQ

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 150 Ω

Resistor Type: General Purpose Resistor

Element Type: Thick Film

Package Size Code: 2512

Power Rating: 1 W

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Resistance Value	150 Ω
Power Rating	1 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	.55 mm[.022 in]
Product Length	6.35 mm[.25 in]
Product Width	3.2 mm[.126 in]

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGCQ2512J150R

150 ohm, Surface Mount General Purpose Resistor, Thick Film, 2512, 1 W, 5 %, ±100 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Neohm CRGCQ



TE Part # 2176349-4
CRGCQ 2512 18R 1%

TE Part # 1-2176350-2
CRGCQ 2512 68R 5%

TE Part # 1-2176345-2
CRGCQ 1210 82R 1%

TE Part # 1-2176347-7
CRGCQ 2010 220R 1%

TE Part # 1-2176341-7
CRGCQ 0805 220R 1%

Also in the Series | [Neohm CRGCQ](#)

[Surface Mount Resistors\(693\)](#)

Customers Also Bought

TE Part #CAT-M8793-T273
MQS, RECEPTACLE AND TAB

TE Part #3-647002-4
04P MTA100 PSTD CONN ASSY LF

TE Part #6-1879497-7
CRGH1206 5% 560R 0.5W

TE Part #1SNK512010R0000
ZS25

TE Part #2213932-2
SMT TB R/A HEADER, 3.5MM, 2 POS

TE Part #2-1445100-4
MICRO MNL HDR ASSY S/ROW LF

TE Part #5554349-1
EMI RCPT ASSY, 24 POS, SHLD

TE Part #280370-1
2P AMPMODU II SHRD HDR, ST, TIN



Documents

Product Drawings

CRGCQ 2512 150R 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176350-4_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176350-4_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176350-4_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CRGCQ Data Sheet

English