



ENGLISH

Datasheet

RS Pro LDM Distance Meter - RSLDM-100H

RS Stock No:126-8184



Accuracy	± 1.5 mm
Battery Life	Up to 4000
Display Type	LCD
Imperial or Metric	Both
Laser Class	Class 2
Laser Wavelength	635 nm
Measurement Range	0.05 to 100 m
Model Number (p)	RSLDM-80H
Power Source	Battery
Weight	100 g

RS Pro LDM distance meters designed for quick, non-contact measurement of areas and volumes of rooms, heights, distances and angles. The device allows direct and indirect measurements where access to the target is difficult.

Features and Benefits

- Immediate or long-term (tracking) measurement of the distance to the target (length)
- Angle measurement
- Indirect distance measurements
- Area and volume determination
- Calculations
- Determination of the maximum and minimum values
- Addition and subtraction of indications
- Automatic storage of the last 20 measurement results
- Laser pointer targets
- LCD display with backlight
- Battery status indicator
- Automatic shut off
- Automatic device off after 3 min of inactivity
- IP54

