



PHYSICAL

Conductors: 28 AWG 7/36 Tinned Copper  
 Insulation: .010" Nom PVC  
 Color Code: Brown, Red, Orange, Yellow, Green, Blue, Violet, Gray, White, Black and Repeat  
 Temp. Rating: 105°C

ELECTRICAL

Voltage Rating: 300 V  
 Current Rating: 1.3 A @ 10°C Rise Above Ambient  
 Insulation Res.: 10<sup>10</sup> ohms – 10 ft Min.  
 Cable Style: UL AWM Style 2693 (105°C, 300V)  
 CSA: Available upon request

Part Number	Count	Width
111-2803-008	8	.28" NOM (7,11mm NOM)
111-2803-010	10	.35" NOM (8,89mm NOM)
111-2803-015	15	.53" NOM (13,34mm NOM)
111-2803-020	20	.70" NOM (17,78mm NOM)
111-2803-030	30	.105" NOM (26,67mm NOM)

For Other Conductor Counts, Contact Factory: Width= .035" X (# of Conductors)

All Dimensions in Inches Unless Otherwise Noted.

REVISION	CHANGES	ECO	DATE
B	ADD 8 CONDCUTOR TO TABLE	8811	6/21/19
A	RELEASE DRAWING	-	12/11/02

  

DRAWN BY		REVIEWED	APPROVED	DOCUMENT NO.	111-2803-0XX		<b>AMPHENOL SPECTRA-STRIP</b> 720 SHERMAN AVENUE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev B
FITTS 12/11/02				TITLE:	Spectra-Bond® Parallel Conductor Cable			SHEET 1 OF 1