

Features

- 2 Gang
- Blank
- White
- Twin Earth
- Urea Mouldings
- White
- Stylish smooth profile plate

RS PRO Plug Sockets

RS Stock No.: 0845490



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 25mm 2 gang back boxes
- Urea mouldings make the socket suitable for use in applications where Antibacterial & Antiviral Certified material is required
- Suitable for use with standard UK 13A plug tops

General Specifications

Plate Dimensions (mm)	146 (W) x 86 (H) x 9.5 (D)
Overall Dimensions (mm)	146 (W) x 86 (H) x 31 (D)
Plate Fixing Centres (mm)	120.6
Style	Rounded Profile
Anti Microbial Certified	Yes
Product Marking	DC, 5V 3A, 5V 2.4A max, 4.2A
Warranty (Years)	25
Warranty - Electronics (Years)	2

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	1.2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
USB Output Type	USB Type 'A' & Type 'C'
USB Number Of Outputs	2
Minimum Back Box Depth (mm)	25
Single Pole Switched	Yes
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13
USB Charging Total Load (A)	4.2
USB Standby Current (mA)	2
USB Charging Voltage (V DC)	5

Approvals

Standards Met | BS 1363-2: 2016 +A1: 2018, BS EN IEC 62368-1, BS EN 62680-1-1