

Datasheet

RS Pro #2030WC Digital Thermometer, 1 Input LCD

RS Stock No: **408-6137**



Product Details

RS Pro digital thermometer comes with 1 input LCD display, 3 m external temperature sensor and 1 x AAA battery. It has °C/°F selectable option and min/max temperature memory.

Features and Benefits

- Wall mountable (bracket included) or desk top (stand)
- Temperature range from -50 to +70°C
- Accuracy of $\pm 1^{\circ}\text{C}$ between the operating temperature of 0 to +40°C
- Resolution of 0.5°C



ENGLISH

Specifications:

Absolute Maximum Temperature Measurement	+70°C
Application	Multi-Purpose
Battery Type	AAA
Best Accuracy	±1%
Minimum/Maximum Recordings	Yes
Number of Temperature Inputs	1
Resolution	0.5°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	LCD
Instrument Measurement Range	-50 to +70°C