



DEWALT DCW200N-XJ –

18V XR Brushless 14 Sheet Orbital Sander - Bare Unit



- Brushless motor offering superb runtime and durability
- Dust port connects directly to DEWALT's Airlock System forming a secure, locking connection between tool and dust extractor, or std. 35mm connector
- Wireless Tool Control allows cord free connectivity to WTC-equipped DEWALT dust extractors
- Textured anti-slip top and body grip provides ultimate comfort and control during use
- Hook & loop platen allows faster paper change, better dust extraction and increase sanding efficiency

Description:

The DEWALT DCW200N-XJ – 18V XR Brushless 1/4 sheet orbital sander provides users with the power and runtime needed to get the job done. A variable, seven-speed dial offers speed control from 8000 – 13500 OPM, allowing users to match the sander's speed to their application. To aid in dust collection, the sander features a one-handed locking dust bag that attaches securely to the sander through its AIRLOCK™-compatible dust port. Alternatively, the user can attach the sander directly to the DCV586M dust collector.

Supplied with:

DEWALT DCW200N-XJ – 18V XR Brushless 14 Sheet Orbital Sander

Fabric dust bag with built-in extractor ports

Paper punch

Specifications	
Orbits Per Minute	8,000 - 13,500 opm
Orbit Size	1.6mm mm
Paper Size	140 x 115 mm
Pad Size	108 x 115 mm
Power Source	Cordless
Product Type	Orbital Palm Sander 1/4 Sheet
Hand/Arm Vibration	3.8 m/s ²
Uncertainty K 1 (Vibration)	1.5 m/s ²
Sound Pressure	76.0 dB(A)
Sound Pressure Uncertainty	3.0 dB(A)
Sound Power	87.0 dB(A)
Sound Power Uncertainty	3.0 dB(A)