

Previously known as: PU610DGAS



Multi Purpose



Light Duty

Antistatic multi-purpose gloves, delivering heightened comfort and dexterity

- **Specialized protection:** With EN 16350:2014 certification for protection from electrostatic discharge, HyFlex® 11-135 antistatic gloves can prevent costly accidents and damage to products
- **Augmented dexterity:** Stretchable stitches and a light, finger-dipped polyurethane coating grant these HyFlex® gloves added dexterity and tactility
- **Considered aesthetics:** HyFlex® 11-135 industrial gloves' polyamide liner boasts high levels of tenacity, producing very little lint despite extensive use
- **Elevated comfort:** A seamless, flexible design also ensures comfortable personal protection
- **Genuine versatility:** HyFlex® 11-135 industrial safety gloves are highly versatile, being touchscreen compatible and appropriate for diverse applications



Industries

- Automotive
- Electronics
- Machinery and Equipment
- Life Sciences

Previously known as: PU610DGAS

Key Features

- **Seamless copper-infused material:** Antistatic hand protection ensured
- **Stretchable stitches and thin PU coating:** For comfort and dexterity
- **High-tenacity polyamide liner:** Low lint levels even with extensive use

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



EN388: 2016



113XA

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
HyFlex® 11-135	Finishing: Fingertip Coated Coating Material: Polyurethane Liner Material: Copper, Polyamide Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699