



Part Number : [732870311](#)
Product Description : 2.92mm Attenuator,
Plug to Jack, Straight, 40 GHz, 0.5 Watt, 3 dB,
with Hex
Series Number : 73287
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[732870311_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 0.5 Watt, 3 dB, with Hex
Keyword	Attenuators
Product Name	2.92mm
Style	Attenuator
Type	Subminiature
UPC	198282629153

Electrical

Attenuation Level (dB)	3
Average Power Max (Watts)	0.5
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.40:1

Physical

Body Style	With Hex
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Wire/Cable Type	N/A