

Datasheet

ECP-45 UK series

45W plug-in power supply



Features

- No load power consumption
- Protections: short circuit//overload voltage//overload current
- UK and European versions available
- Compact and light-weight
- Withstands operating environment of 0-40°C
- Efficiencies up to 86%
- 3 year warranty
- External switch mode plug-top power supplies
- Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- Energy saving power supply
- Class II double insulated
- 1.2 metre (approx.) output lead with 2.1x5.5x9.5mm centre positive output connector
- Regulated output
- EMC compliance to EN 55022 Class B

Part number	Voltage	Rated current	Voltage range	Rated power	MTBF
7263012	12V	3.75A	11.4 ~ 12.6V	45W	100,000hrs min. MIL-HDBK - 217F (25°C)
7263015	15V	3A	14.25 ~ 15.75V		
7263019	18V	2.5A	17.1 ~ 18.9V		
7263028	24V	1.88A	22.8 ~ 25.2V		

Mechanical specification

