

**Low Profile**
T&B Catalog Number:

SF100-18X-100

UPC Number:

78621019176

Status:

Active

Description:

Cable Tie 18lb 4.7" Blk Low-Profile 1-Pc

Features

Low-Profile, contoured head reduces clearance required for the bundle and enhances the appearance of your harness.

The safeguard wall eliminates exposure to sharp edges.

The saddleback fits snug against the contour of the wiring harness.

General

Material	Nylon 6.6 Weather Resistant
----------	-----------------------------

Color	Black
-------	-------

Dimension Information

Nominal Length (inches)	4
-------------------------	---

Length (inches)	4.65
-----------------	------

Width (inches)	0.095
----------------	-------

Max. Wire Bundle Diameter (inches)	1
------------------------------------	---

Min. Wire Bundle Diameter (inches)	0.125
------------------------------------	-------

Thickness (inches)	0.043
--------------------	-------

Specifications

Temperature Rating	-40°F to 185°F
--------------------	----------------

Flammability Rating	UL 94 V-2
---------------------	-----------

Packaging

T&B Order Multiple	100
--------------------	-----

T&B Inner Pack	100
----------------	-----

Package in Units	1000
------------------	------

Package Type	Regular
--------------	---------

T&B Sold in UOM	Each
-----------------	------

T&B Weight Per UOM	0.63 lbs. per 1000
--------------------	--------------------

Application Support

Overview	Available on Website
----------	----------------------

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com