



Fuse-link, low voltage, 63 A, AC 660 V, DC 460 V, 80 kA, BS88, 27 x 112 mm, gL/gG, BS

Part no. 63A 660V AC / 460V DC IND FUSE
Catalog No. TB63

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	63
Rated voltage			AC 660 V DC 460 V
Construction size			BS88
Size			27 x 112 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Standards/Regulations			BS88 IEC 60269

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	63
Rated voltage		V	660
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No