



DWE6411

1/4 SHEET ORBITAL SANDER

Features and Benefits

- 230 Watt motor sands at 14,000 orbits per minute, providing a superior finish
- Hook & loop platen allows faster paper change, better dust extraction and increase sanding efficiency
- Paper clamps provided for conventional abrasives
- Textured anti-slip top and body grip provides ultimate comfort and control during prolonged use
- Dust sealed switch for increased durability
- Sealed 100% ball-bearing construction provides longer life
- High capacity dust bag with built in vacuum adapter
- Dual plane counter-balance low-vibration design reduces user fatigue

Standard Equipment

- Dust bag with built-in extractor connection

Specifications	
Power Input	230 Watts
Orbits Per Minute	14000 opm
Orbit Size	1.6 mm
Paper Size	140 x 115 mm
Pad Size	108 x 115 mm
Hand/Arm Vibration	4.0 m/s ²
Length	160 mm
Height	135 mm