

Metal drill bit sets HSS PointTeQ

- ▶ Twist drill bit made of high-speed steel
- ▶ Right-hand cutting twist drill bit, Type N, 135° from 4 mm upwards (below 118°)
- ▶ Shank equal to drill bit diameter
- ▶ Two-cutter, cylindrical, two flutes

PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
5-piece Metal HSS PointTeQ Twist Drill Bit Set							
Shank diameter equal to drill bit diameter							
2	24	49	P1c	5	1	3165140917636	2 608 577 345
3	33	61					
4	43	75					
5	52	86					
6	57	93					

