




General characteristics

Colour	Grey
Type of positions	Flush pushbutton
Material	Polycarbonate
IEC degree of protection	IP66, IP67, IP69K

Ambient conditions

Temperature	Operating temperature	min	°C	-25
		max	°C	+70
	Storage temperature	min	°C	-40
		max	°C	+85

Dimensions



Certifications and compliance

Certificates	cULus
--------------	-------

ETIM classification

ETIM 8.0

EC000225 -
Control circuit
devices
combination in
enclosure