



CONTINUITY INDICATOR TEK404

SPECIFICATIONS

Probe Voltage: 9V.

Test Current: 5mA.

RESOLUTION

Range: 0 - 170k ohms audible, 0 - 8k ohms visual.

Output: 85dB minimum at 30cm, zero resistance. Red LED illuminates below 8k ohms.

Audible Frequency: 2.8kHz \pm 0.1kHz. Internal safety cutout protects 500V AC/DC.

It is supplied with unfused leads (TL49). Fused leads (TL56) are also available for extra operator safety.

Requires a PP3 battery.

[Back to Continuity Indicators](#)