MCS-112X90-C-D-1018 - Housing frame

1524261

https://www.phoenixcontact.com/in/products/1524261

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing frame, Design element with marking field, color: yellow (similar RAL 1018)

Your advantages

- Convenient operation during device installation and maintenance thanks to optional hinges on the housing cover
- Flexible mounting thanks to the optional adapter plate
- Safe operation with the right degree of protection
- Individualized product selection due to the modular system
- Optimized PCB installation: PCB can be installed in a nearly horizontal orientation thanks to the angled housing edge

Commercial data

Item number	1524261
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	ACFFAB
GTIN	4063151991609
Weight per piece (including packing)	21.5 g
Weight per piece (excluding packing)	15.6 g
Country of origin	DE

Technical data


Notes

Assembly note	Please observe the assembly instructions available in the download area.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Cover
Housing type	Field housing
Housing series	MCS
Product family	MCS-112X90
Ventilation openings present	no

Dimensions

Dimensional drawing	
Dimensions	112.6 mm x 90.6 mm x 8 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Material Housing	PA-GF
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Mounting


Mounting type	Latching with upper housing part
Mounting position	any

Packaging specifications

Type of packaging	Box packaging

Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in