

**ZM35** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M35X1,5	Thread
D	52 mm	Outside diameter
h	12 mm	Height
M _A	5 Nm	Mounting torque set screw
F _{aB}	134,000 N	Breaking load, axial
M _L	80 Nm	Breakawag
M _{AL}	40 Nm	Mounting torque reference
M _M	0.537 kg*cm ²	Mass moment of inertia
≈m	0.101 kg	Weight

Dimensions

d ₁	47 mm	Plant diameter outside
t	2 mm	Hight retaining slot
b	5 mm	Width retaining slot
c	6 mm	Distance bore
m	M6	Threaded - threaded pin