

Datasheet

Stainless Steel Threaded Straight Increaser, 1/4 in R Male, 1/2 G Female

RS Stock number [3108703](#)



Features

- Male to female increaser
- Maximum working pressure: 150 bar
- Body: Stainless steel 316L

Specifications

- Working Temperature: -20 to 180 °C
- Connection 1: 1/4in R Male
- Connection 2: 1/2in G Female
- Connection Gender 1: Male
- Connection Gender 2: Female
- Fitting Direction: Straight
- Fitting Type: Increaser
- Thread Size 1: 1/4in
- Thread Size 2: 1/2in
- Thread Standard 1: R
- Thread Standard 2: G

Measurements

- C1: R1/4
- C2: G1/8
- E (mm): 15
- F (mm): 27
- L1 (mm): 32.5
- Weight (kg): 0.069

