

Brush Cutter XGT®

UR006G

40Vmax • 0 - 4600 / 5500 / 7000 min⁻¹

Powerful XGT® Grass trimmer with bike handle for various applications.

UR006G has a brushless motor and 3 - speed (Low/ Medium/High) motor system. Reverse rotation system allows operator to quickly clear trimmer head / blade of entangled grass and weeds. Soft start feature for added motor protection.



XGT **BL** **ADT** **AFT**
MOTOR

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 4600 / 5500 / 7000 min ⁻¹
Cutting width	255 / 305 / 430 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	U
Sound Power Level (L _{WA})	88,4 - 95,4 dB(A)
Sound Pressure Level (L _{pA})	77 - 82,9 dB(A)
Noise Uncertainty (K Factor)	0,5 - 2,4 dB(A)
Product net weight	4,9 kg
Tool weight with battery	5,7 - 6,9 kg
Product Dimensions (L x W x H):	1815 x 677 x 540 mm
Nylon line- Diameter	2,0 / 2,4 mm

User benefits

- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Soft start feature for added motor protection
- Constant speed control maintains constant speed under load
- Rear end mounted motor makes the tool balance similar to engine grass trimmers

Link to product - www.makitauk.com



Related products

Optional AC

191D90-9

Trimmer Head 2,4 mm, M10 x 1,25



198383-1

Plastic Blade set, 255 mm



D-66064

2-Tooth Brush cutter Blade



Other

[User manual](#)

[Parts drawing](#)