

S 1500 ES-03 MODULE ASSORTMENT LARGE

325 pieces

- > Extensive industrial range for professionals
- > Tools in metric sizes
- > Proved GEDORE ES tool modules from ABS
- > For tool trolleys 2005 models 0810, 2004 models 0810, 1000
- > For workbench 1504 models 0810, 1000, 1504 XL, 1506 XL models 2511, 2810
- > Also available in tool trolley 2004 0810



2004 0810



























Contents				Code	No.
1500 ES-1 B	1500 ES-400	8551-55	2319861	S 1500 ES-03	S 1500 ES-03
1500 ES-19 IS	1500 ES-6	H 42 KEL-88			
1500 ES-1993 U-20	1500 ES-7 R	H 43 KTX-07			
1500 ES-2	1500 ES-711	8728			
1500 ES-2 B	1500 ES-8000	60 P 8			
1500 ES-20	1500 ES-DT 42	137 10			
1500 CTD-20 BIT	1500 ES-IN 19 LKM	4615 3			
1500 ES-2133	1500 ES-ITX 19 LKP	0513-09			
1500 ES-2150 PH	1500 ES-K 1900	1940			
1500 ES-2163 TX	1500 ES-VDE 145				
1500 ES-34	1500 ES-VDE 2170 PZ				
1500 ES-350					
1500 ED-70 K [7x]					
S 1500 ES-03			2657716	1500 ES-03 2004	1500 ES-03 2004 0810
+ 2004 0810					

























	Contents
	1 B 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22
	42 2 (S/64AF) 2,5 3 4 5 6 8 10
	19 10 11 12 13 14 15 16 17 18 19 21 22 23 24 26 27 28 30 32
	IS 19 10x1,6 12x2
	IKS 19 2 3 4
	INX 19 8 10
	1993 U-20

	Contents
	1987
	1995
	1990 -5 -10
	2 6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22
	2 B 6x7 8x9 10x11 12x13 14x15 17x19
	2093 U -10
	2087

	Contents
	2090-4
	2095
	2098
	20 4 5 5,5 6 7 8 9 10 11 12 13 14
	IN 20 3 4 5 6 8
	TX 20 E4 E5 E6 E7 E8 E10
	ITX 20 T8 T9 T10 T15 T20 T25 T27 T30 T40



Contents	
	20 L 4,4,5 5 6 7 8 9 10 12 13
	680 4-25 5,5-25 6,5-25 8-25
	685 2,5-25 3-25 4-25 5-25 6-25
	685 X 5-25 6-25 8-25
	687 TX T6-25 T7-25 T8-25 T9-25 T10-25 T15-25 T20-25 T25-25 T27-25 T30-25 T40-25
	690 1-25 2-25 3-25
	690 PZD 1-25 2-25 3-25
	673 6,3
	699
	620
	676
	639
	TFK 649 E-649 F
	2133 5,5 6 7 8 9 10
	2150 4 5,5 6,5 8
	2160 PH 1 2
	2163 TX T8 T10 T15 T20 T25 T30
	34 8x9 10x11 12x13 14x15 16x17
	97 -250
	98 -125
	99 12-5
	100 -12
	119 -1,5 -3 -4
	600 H -300

Contents	
	400 8x10 10x11 12x14 17x19 13x15
	6 6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27
	7 R 8 10 12 13 14 15 16 17 18 19
	140
	4534 -5
	708
	711
	720
	745
	8000 A 1 2 21
	8000 J 1 2 21
	DT 2142 2,2,5 3 4 5 6 7 8 10
	IN 19 5 6 7 8 9 10 12 14 17
	IN 19 L 5-90 6-90 8-90 10-140 12-140 14-140
	ITX 19 T20 T25 T27 T30 T40 T45 T50 T55 T60
	ITX 19 L T20-100 T25-100 T27-100 T30-100 T40-100 T45-100 T50-100 T55-100 T60-100
	708
	K 19 10 13 14 17 19
	880 7 8 9 12
	885 5 6 8 10
	890 1 2 3 4
	KB 819
	K 1900
	142 10 C

Contents	
	VDE 8250 -180 H
	VDE 8132 -160 H
	VDE 8314 -160 H
	VDE 2170 4,5,5 6,5 8
	VDE 2160 PZ 1 2
	8551 1 2 3 4 5
	42 KEL 2,2,5 3 4 5 6 8 10
	43 KTX T10 T15 T20 T25 T27 T30 T40
	8728
	60 P 8
	137 10
	4615 3
	0513-09
	1940
	1500 ED-70 K [7x]