

- Provides a variable voltage output proportional to the position of the pedal
- Utilising a solid state optical sensor with no moving parts or tracks which can wear out
- Black cover & base
- Complete with 2 meters of grey 3 core cable
- Momentary action
- Sealed to IPX2
- Electrical rating: 4.5V to 12V at 10mA
- Output voltage range: 6% minimum to 95% maximum of input voltage
- Output current 100uA / transistor sink/source
- Operating Temperature: 0°C to +40°C



### Outline Dimensions

