

PRODUCT-DETAILS

## 2601/6 W-54

### 2601/6 W-54 Rocker switch 1gang 2way



#### General Information

Extended Product Type	2601/6 W-54
Product ID	2CKA001085A1628
EAN	4011395083710
Catalog Description	2601/6 W-54 Rocker switch 1gang 2way

#### Ordering

EAN	4011395083710
Customs Tariff Number	85365080
Minimum Order Quantity	1 piece

#### Dimensions

Product Net Depth / Length	5.5 cm
Product Net Height	8.3 cm
Product Net Width	7.4 cm
Product Net Weight	0.119 kg

#### Container Information

Package Level 1 Units	10 piece
Package Level 1 Depth /	0.315 m

**Length**

Package Level 1 Height	0.116 m
Package Level 1 Width	0.184 m
Package Level 1 Gross Weight	1.38 kg
Package Level 2 Units	100 piece
Package Level 2 Depth / Length	0.596 m
Package Level 2 Height	0.331 m
Package Level 2 Width	0.393 m
Package Level 2 Gross Weight	14.633 kg
Package Level 3 Units	1200 piece
Package Level 3 Depth / Length	1.2 m
Package Level 3 Height	1.143 m
Package Level 3 Width	0.8 m
Package Level 3 Gross Weight	195.596 kg

**Technical**

Degree of Protection	IP44
Mounting Type	Surface Mounted

**Certificates and Declarations (Document Number)**

Declaration of Conformity - CE	2CKA100000E0218
RoHS Information	9AKK104295D8727

**Environmental**

RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
-------------	---

**Classifications**

ETIM 7	EC001590 - Switch
ETIM 8	EC001590 - Installation switch
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany (DE)

**Categories**

Low Voltage Products and Systems → Switch Assortments → Light / LoadControl → Mechanical Switch / Push Button → Mechanical Switch / Push Button - Flush Mounted → Mechanical Switch / Push Button

Low Voltage Products and Systems → Switch Assortments → Surface Mounted Range → Surface Ranges Waterproof IP44 → Design Ocean → Mechanical Switch / Push Button

