



mecalectro

## Electromagnet for retaining or handling parts – 5.85.01



**Diameter:** 90 mm

**Holding force when power on:** 294 daN

**Power Consumption:** 20 W

**Total mass:** 2200 g

**Degree of protection / Energetic class:** IP 40 / B

**Standard supplies:** 24Vcc

**Possibles supplies:** From 12 to 220Vcc

**Duty Cycle:** Permanent (100%)

**Standard:** NF C 79300

**Examples of applications:** Maintaining parts, blocking parts, positioning, gripping.