



## Main

|                             |   |
|-----------------------------|---|
| Range of product            | Harmony XAP   |
| Product or component type   | Die-cast empty control station  |
| Device short name           | XAPM  |
| Product destination         | For Ø 30.5 mm control and signalling units  |
| Product front plate size    | 80 x 80 mm  |
| Usable depth                | 74.5 mm   |
| Number of cut-out           | 1 cut-out   |
| Colour of base of enclosure | Blue  |
| Colour of cover             | Blue  |
| Material                    | Zinc alloy  |
| Cable entry                 | 1 hole with blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm<br>1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm |
| Device mounting             | Flush   |
| IP degree of protection     | IP65 conforming to IEC 60529<br>IP69 conforming to NF C 20-010<br>IP69K   |

## Complementary

|                         |   |
|-------------------------|---|
| Number of vertical rows | 1 |
|-------------------------|---|

## Environment

|                                       |  |
|---------------------------------------|--|
| Protective treatment                  | TC   |
| Ambient air temperature for storage   | -40...70 °C  |
| Ambient air temperature for operation | -40...70 °C  |
| Overvoltage category                  | Class I conforming to IEC 60536<br>Class I conforming to NF C 20-030 |

## Packing Units

|                  |          |
|------------------|----------|
| Package 1 Weight | 725 g    |
| Package 2 Weight | 9.036 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           |  <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information |  Yes  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>   |

---

|                          |   |
|--------------------------|---|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |
| Circularity Profile      | <a href="#">End Of Life Information</a>       |

---

### Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---