


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2012002040](#)
Status: **Active**
Overview: [Spot-On Wire-to-Board Connector System](#)
Description: [Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, 4 Circuits, Natural](#)

Documents:

3D Model	Product Specification 2012000000-PS-000 (PDF)
Drawing (PDF)	Packaging Specification 2012009200-200 (PDF)
Product Specification 2011960000-A00 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2011960000-A01 (PDF)	



General

Product Family	Crimp Housings
Series	201200
Application	Signal, Wire-to-Board
Overview	Spot-On Wire-to-Board Connector System
Product Name	Spot-On
UPC	191128252140

Physical

Circuits (maximum)	4
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	567.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2012009200-200
Product Specification	2011960000-A00, 2011960000-A01, 2012000000-PS-000
Sales Drawing	2012002060-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201200 Series](#)

Mates With

Spot-On Header [201201](#)

Use With

Receptacle Terminal [201195-6000](#)