



"x"	Switch function
B	on - (mom)
C	off - mom

Specifications:

Contact rating: 1A, 250V AC / 3A, 125V AC
 2A, 24V DC
 Contact resistance: 30mOhm max.
 Insulation resistance: 500MOhm min. at 500V DC
 Dielectric strength: 1 000V, 50Hz for the duration of 1 minute
 Operating temperature: -45°C to +110°C
 Mechanical life: min. 30 000 cycles
 Soldering conditions: hand-soldering: max.: 305°C, 3sec., 20W
 Mounting: bushing M6x0.75
 Material: Contacts: coin silver
 Terminals: solder tags



Tolerances:			Date	Name	<h1>MSP 103 xK</h1>
			11/08	dr	
			knitter-switch		<h2>20 09 05</h2>
Modifications			Date	Name	Page 1/1