



Main

Range	Mureva
Product or component type	Socket
Device short name	Mureva socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Panel-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	100...130 V
Network frequency	50/60 Hz
Ground lug clockwise position	4 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: brass
Connections - terminals	Captive screws
Cable cross section	1...4 mm ²
Net weight	0.147 kg
Base dimension	65 x 85 mm
Height	85 mm
Width	73 mm
Depth	103 mm
Colour	Grey (RAL 7035)
Voltage colour	Yellow

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations