



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 1 Ω

Resistor Type: **General Purpose Resistor**

Element Type: **Thick Film**

Package Size Code: **0603**

Power Rating: **.1 W**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Resistance Value	1 Ω
Power Rating	.1 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.6 mm[.063 in]
Product Width	.8 mm[.031 in]



Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (2.71% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRG0603F1R0

1 ohm, Surface Mount General Purpose Resistor, Thick Film, 0603, .1 W, 1 %, ±200 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Neohm CRG



TE Part # 1623097-1
[CRG0805 1% 10K](#)



TE Part # 1623404-1
[CRG1206 1% 10K](#)



TE Part # 1622829-1
[CRG0603 1% 10K](#)



TE Part # 1676480-1
[CRG0402 1% 100K](#)



TE Part # 1-1622826-8
[CRG0402 5% 1K0](#)

Also in the Series | [Neohm CRG](#)



[Surface Mount Resistors\(614\)](#)


Customers Also Bought



TE Part #650126-000
[D-436-82](#)



TE Part #1676480-4
[CRG0402 1% 110K](#)



TE Part #5-103735-5
[06 MTE HDR SRST LATCH .100CL](#)




TE Part #3-2176372-0
[RQ 0603 100K 0.1% 10PPM 5K RL](#)



TE Part #322799
[SOLIS R HR 22-16COM22-18MIL 10](#)



TE Part #5-1879337-9
[CPF 0603 10K 1% 50PPM 1K RL](#)




TE Part #1217421-1
[250 FASTON,PCB TAB,TNBR](#)



TE Part #1622987-1
[CRG0603 1% 68K](#)



TE Part #BAT-HLD-013-SMT-TR
Hldr for CR2032 Battery, SMT, T&R Pkg



TE Part #2195932-1
FPC, ANT, LTE, SLEEVE

Documents

Product Drawings

CRG0603 1% 1R0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1622878-4_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1622878-4_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1622878-4_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Thick Film Chip Resistors - Type CRG series

English