



## Solenoid - 8.02.13.62

Type > Pull or push



Stroke : 4 mm  
Force at nominale stroke : 2 N  
Power consumption at 100% : 4 W  
Total mass : 30 g  
Degree of protection : IP 40  
Energetic class : B  
Standard supplies : 24Vcc  
Possibles supplies : From 6 to 48 Vcc  
Duty cycle : Permanent, impulsions (100, 40, 25, 15, 5 %)  
Exemples of applications : Automatismes, blocage, compostage, distribution.