

Soft Polyurethane, Metric Size - TUS

TUS0805Y-20

Datasheet

General series information

- Applicable tubing O.D.: Ø 4 to Ø 12 mm
- Operating temperature: -20 to 60 °C for air
- 8 colour variations.

Standard specifications

Size	0805 (O.D. Ø8 I.D. Ø5)
Color	Y (Yellow)
Roll Length	20 m Roll
Pressure medium	Air
Maximum temperature of pressure medium	20 °C
Maximum operating pressure	0.6 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-20 °C (with no freezing)
Usable tubing material	Polyurethane
Weight	0.700 Kg

Additional information

Catalogue

[T_EU.pdf](#)