

# HP10R

## RECHARGEABLE PURE BEAM FOCUSING

1050 LUMENS | 310M BEAM | 11H



BATTERY TYPE	1 x Lithium Ion / 4 x AAA (Alkaline)	LIGHT OUTPUT (HIGH)	1050 Lumens
BEAM DISTANCE (HIGH)	1017 ft / 310 m	LIGHT OUTPUT (LOW)	230 Lumens
BEAM DISTANCE (LOW)	475 ft / 130 m	RUNTIME (HIGH)	6 h
		RUNTIME (LOW)	11 h
INCLUDED	1 x Li Ion Battery   4 x AAA Batteries   AC+DC with USB adapters   Sheath   Lanyard	WEIGHT	11 oz / 312 g

The HP10R brings over 1000 lumens of rechargeable power to a Pure Beam Focusing LED flashlight. Equipped with our Pure Beam Focusing Optic with Slide Focus, users can shift between a super wide flood beam or spot mode with transition halo at varying distances and brightness all controllable with one hand. For those looking for tactical features, this light includes a strobe in between the high and low light modes. The Beam Lock System also ensures that users keep the beam in place while they work without risk of losing the perfect lighting. With our Flex Charge Dual Power system, this light harnesses either lithium or alkaline power and using a micro USB. A USB insert on the battery and tail cap allows for the recharging of the batteries either inside or outside of the light. A USB power out under the Pro-Tek tail cap will enable users to recharge devices that use USB charging cords.

With Coast's commitment to quality, the HP10R Flashlight is impact resistant, weather resistant and its LED is virtually unbreakable. The HP10R Flashlight is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.



### BEAM LOCK

Set the beam to stay how you like it. COAST Beam Lock technology makes our Slide Focusing system even more valuable, with the option to lock the beam in place on spot, flood, or anywhere in between. Twisting the head of the light to the left locks the beam in place, and twisting it back to the right releases the slide mechanism back into motion.



### DUAL POWER

Options to stay ready. With COAST Dual Power technology, you have the choice to power your light with USB-rechargeable batteries or with standard alkaline batteries.



### EXTERNAL DEVICE CHARGING

Power any USB-enabled device. Select COAST lights feature a special external charging system that allows other devices to recharge from an easy-to-carry COAST handheld battery pack.



### FLEX CHARGE

Power up on your terms. Lights with COAST Flex Charge technology feature a rechargeable battery that can be recharged either inside or outside the light. A simple USB connection to either AC or DC ensures you can always get juice.



### HIGH STROBE LOW

Control your light power with the push of a button. Cycle between full light, strobe and low light options.



### PURE-BEAM FOCUSING OPTIC

Pack two powerful beams into one and seamlessly transition—with no halos or hot spots—between short and long-range viewing. COAST's patented focusing technology adapts to your need. The Ultra View Flood beam delivers edge-to-edge clarity in a broad circle of light up to 11.5 feet / 3.5 meters across, and the Bulls-Eye Spot beam sends a sharp ray of light at a distance of up to 1151 feet / 351 meters, with a transitional halo around the spot to increase the effective viewing area.



### SLIDE FOCUS

One-handed beam control. COAST's Slide Focus system enables you to seamlessly transition between spot and flood beam with the push or pull your finger. Responsive beam-shape control allows you to operate your light with a single hand and keep the other hand free.



### WATER RESISTANCE

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.