

FEATURES

- **Non-Releasable Design:** Provides a secure and permanent fastening solution
- **UV Resistant:** Suitable for outdoor applications, resisting degradation from sunlight
- **High Tensile Strength of 36 kg:** Ensures strong and reliable bundling
- **Made from Nylon:** Offers durability and flexibility
- **Fire Behaviour UL 94 V-2:** Meets safety standards for flammability
- **Maximum Bundle Diameter of 83 mm:** Accommodates a wide range of cable sizes
- **Operating Temperature up to 85°C:** Suitable for various environments

RS PRO Nylon Cable Tie, 300mm Non-Releasable

RS Stock No: 656-061



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a robust nylon cable tie designed for secure and efficient bundling of cables and wires. With a length of 300 mm, this non-releasable cable tie is ideal for applications requiring a strong and durable fastening solution. Its UV-resistant properties make it suitable for both indoor and outdoor use, ensuring longevity and reliability.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	36 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	83 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---