



## DATASHEET

### SPRING LOADED TOGGLE LATCH 40023 ZI



#### DESCRIPTION:

Available with or without padlock facility.

Interchangeable with American models

Wide positioning tolerance created by spring mechanism

Failsafe design prevents over extension of links

Maximum operating tension: 45daN

Suitable for screw fixing using 2xM5 screws for latch and 2xM5 screws for catch

Supplied with catch.

#### FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 75 x 47,5 x 20,5 mm
- Depth: 20,5 mm
- Length: 75 mm
- Width: 47,5 mm

