

FEATURES

- Oil-filled radiator
- Dimensions of 660 mm (H) x 370 mm (W) x 165 mm (D)
- Convection heating
- Floor mounted
- Thermostat control
- Three power settings
- Type C European plug
- Maximum output power of 2 kW
- Wheels for easy rolling transport

2kW Oil Filled Radiator, Floor Mounted, Type C - European Plug

RS Stock No.: 712-6086



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Keep rooms in your house or workplace warm with this 2 kW oil-filled radiator from RS PRO. Easily move the heater to where it's needed with the handy wheels on the base. Transportable and slim, this heater will quickly heat your space and has easily-adjustable thermostatic controls so you can reach your desired temperature. Suitable for warming confined spaces, it's electrically powered through a European Type C plug. It helps keep costs down as it lets you focus heat on particular rooms. Thanks to its with excellent thermal retention, less energy is needed to top up temperatures.

General Specifications

Heat Type	Convection
Control Type	Thermostat
Power Settings	3
Safety Thermostat	Yes
Thermal oil	Yes
Applications	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

Electrical Specifications

Maximum Output Power	2KW
Voltage Rating	220V to 240V
Frequency	50Hz
Plug Type	Type C European plug

Mechanical Specifications

Mounting	Floor Mounted
Dimensions	660mm x 370mm x 165mm
Height	660mm
Width	370mm
Depth	165mm

Approvals

Compliance/Certifications	ANSI/ESD S20.20:2014, BS EN 61340-5-1:2007, RoHS
----------------------------------	--



C