



DYNATECH® single torque torque wrenches with removable ends

DYH-5
DYH-...

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:01





DESCRIPTION

DYNATECH® single torque torque wrenches with removable ends

NEW SPRING WITHSTANDING: 1,000,000 cycles of fatigue tests at the max. torque for each wrench. EASY-TO-USE TOOL: thanks to a direct, ergonomic grip. WITHSTANDS EVERY TYPE OF WORKING ENVIRONMENT: thanks to its all-steel design.

Wrench ensuring unfailing repeatability for your safety. This single-torque value wrench has been developed to meet the needs in production and allows you to use all your round end-fittings. Range going from 1 to 350 Nm. ERGONOMIC: Handle that withstands hydrocarbons, solvents, brake fluid and paraffin. Efficient, comfortable grip for the operator, reducing risks of musculoskeletal disorders. Round handle fitting. PRECISION: Precision guaranteed to within +/- 3% for up to 5,000 cycles, i.e. 25% better than the requirements of standard ISO 6789-1 (except models with capacities of 1-5 Nm: +/- 6%). Setting of the torque tightening value thanks to the SAM calibration bench (BC-5N + DYC-...N + DYB + DYT-KIT1). Wrench supplied with 1-point calibration certificate and in a plastic case. Each wrench is numbered and supplied with a verification report in compliance with standard NF EN ISO 6789. Mechanical click-type wrench. Type II - Class B. This is a single-value torque wrench, so please indicate your desired tightening torque value (Nm) when placing your order.

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>



STANDARDS / DIRECTIVES

NF ISO 6789-1

SPECIFIC DATA

Designation	TORQUER WRENCH DYNATECH 1-5 NM FOR ROUND ENDS
Sales reference	DYH-5
Weight (kg)	0.38
Capacity (Nm)	1-5
Ends	12
only wrench length	220
Length with ratchet (mm)	-
Guarantee	M

Guarantee applied

M1 | SAM Equipment and Machine Guarantee:

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de Rochetaillée
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 €

<https://www.sam-outillage.fr/>

Photos and texts not contractually binding. Do not litter. Document generated on 2023-10-26 12:37:01

