



IR FFL

INTERNAL RECHARGEABLE FOLDING FLOOD LIGHT

500 lumens of TRUEVIEW™ high definition output delivers consistent beam, optimised colour temperature and true representation of colours & details

3 modes to manage output and run time

Can be mounted with double magnet or hanging the light with an integrated carabiner hook gives more versatility

Compact size allows easy storage in pocket

IP54 rating, light is protected from dust and splashing water

Impact and chemical resistant lens for more durability on the job site

Safety blinking feature allows end user to be informed of low battery status

Conveniently charge MILWAUKEE® RECHARGEABLE internal battery with USB-C cable from USB power source or AC outlet (wall plug not included)

Job site tough USB-C braided cable with metal ends

Includes USB cable



Max. light output Area Mode	500/ 250/ 100
High Medium Low [lumens]	
Max. runtime high medium low	4/ 8/ 12
Weight (kg)	0.28
Kit included	Integrated battery, USB cable, No kitbox or bag supplied
Article number	4933493528

