

1420826
<https://www.phoenixcontact.com/gb/products/1420826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M12, Rear mounting, M15 x 1, THR- und Wellenlötkontakte, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239326

Your advantages

- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Efficient PCB assembly: two-piece connectors for THR soldering

Commercial data

Item number	1420826
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQADC
Product key	ABQADC
GTIN	4055626280394
Weight per piece (including packing)	12.017 g
Weight per piece (excluding packing)	10.308 g
Customs tariff number	85366990
Country of origin	DE

SACC-BP-M-M12/M15-6-THR PW - Housing screw connection



1420826

<https://www.phoenixcontact.com/gb/products/1420826>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

Product properties

Product type	Panel mounting base
Thread type	M12

Connection data

Connection method	THR- und Wellenlötkontakte
Tightening torque	1.5 ... 2 Nm

Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Seal material	FKM

Connector

Connection 1

Head design	Pin
Head thread type	M12

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Mounting

Mounting type	Rear mounting M15 x 1
---------------	-----------------------

SACC-BP-M-M12/M15-6-THR PW - Housing screw connection



1420826
<https://www.phoenixcontact.com/gb/products/1420826>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-BP-M-M12/M15-6-THR PW - Housing screw connection



1420826

<https://www.phoenixcontact.com/gb/products/1420826>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	05e11741-e87c-4ff9-ba6e-ab320d176d13

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk