



Hand protection

VENITACTYL V1450B100

DISPOSABLE

Disposable chemical glove with good resistance to chemicals and viruses, ideal for the food industry



Specific benefits



Easy to use

· Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use



Hygiene

· Latex-free to reduce the risk of allergies



Performance

· Lightweight for optimal dexterity

Technologies & labels



DMF-free



Silicon-free

Applications

- Agriculture
- Finishing works / Craftsmanship
- Manufacturing/Transformation
- Accomodation & Food services
- Maintenance
- Automotive

Certifications and norms



EN ISO 374-1

TYPE B
JKT



EN ISO 374-5



Protects against risks



Biological



Chemical



Particules



Hand protection

VENITACTYL V1450B100

DISPOSABLE

Disposable chemical glove with good resistance to chemicals and viruses, ideal for the food industry

Standards - Details



EN 374

J
K
T

Technical details

Glove kind	Tight glove
Glove family	Tight glove disposable powder free
Tight glove kind	Disposable
Inner finition	Powder free
Coating material and finition	Smooth nitrile
Coating level	Fully coated
Number of layer	Single layer
Thickness (mm)	0,07
Arm level protection	Standard cuff (< 290mm)
Benefits element	Free latex, Silicone free
Color	Black
Size	6, 7, 8, 9, 10, 11
Type of packaging	Box of 100



Safety gloves

VENITACTYL V1450B100

DISPOSABLE

Disposable chemical glove with good resistance to chemicals and viruses, ideal for the food industry

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
V1450B10006	Black	6/7	VENITACTYL V1450B100	3295249202682	13295249202689	10	1	4.4 kg	26.0 cm	34.4 cm	25.4 cm
V1450B10007	Black	7/8	VENITACTYL V1450B100	3295249202699	13295249202696	10	1	4.8 kg	26.0 cm	34.0 cm	25.4 cm
V1450B10008	Black	8/9	VENITACTYL V1450B100	3295249202705	13295249202702	10	1	5.1 kg	26.2 cm	34.0 cm	25.2 cm
V1450B10009	Black	9/10	VENITACTYL V1450B100	3295249202712	13295249202719	10	1	5.3 kg	26.0 cm	34.0 cm	25.0 cm
V1450B10010	Black	10/11	VENITACTYL V1450B100	3295249202729	13295249202726	10	1	5.6 kg	26.4 cm	34.2 cm	25.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height