

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Sercos III patch cable, shielded, star quad, AWG 22 stranded (7-wire), RAL 3020 (traffic red), RJ45 plug/IP 20, straight, to RJ45 plug/IP20, straight, length: 2.0 m

Commercial Data

Item number	1402516
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	ABNAAT
Product Key	ABNAAT
Catalog Page	Page 321 (PC-2011)
GTIN	4046356622554
Weight per Piece (including packing)	163.1 g
Weight per Piece (excluding packing)	151.1 g
Customs tariff number	85444210
Country of origin	PL

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Technical Data

Product properties

Product type	Data cable preassembled
Number of positions	4
Application	Standard
Locking type	Push Pull
Shielded	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	1

LED signaling

Status display	No
----------------	----

Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Handle color	black
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PA (Contact carriers)
	PA (Housing)
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 80 °C

Connection 2

Handle color	black
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PA (Contact carriers)
	PA (Housing)
Insertion/withdrawal cycles	≥ 750
Ambient temperature (operation)	-25 °C ... 80 °C

Cable / line

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Cable length	2.00 m
Cable type	PROFINET type B
Cable type	Round cable

Ambient conditions

Degree of protection	IP20
Degree of protection	IP20

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Approvals



EAC

Approval ID: 19060508

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Classifications

ECLASS

ECLASS-9.0	27060308
ECLASS-10.0.1	27060308
ECLASS-11.0	27060308

ETIM

ETIM 8.0	EC002599
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Patch cable - VS-PNRJ45-PNRJ45-93K-2,0



1402516

<https://www.phoenixcontact.com/gb/products/1402516>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk